Mobile cold gas UV analyser





Mobile cold-dry gas analyser for power plant optimisation, low concentration measurement and process control

APPLICATION

The UV analyser UVA 17 CD m can be used for monitoring of e.g. NO, NO_2 , SO_2 and O_2 in incineration plants as well as for process measurements in the chemical and pharmaceutical industry.

This analyser is based on a spectrometer and measures all UV absorbing gas components. The applied Xenon flash light is characterised by a 2 to 3 times higher lifetime compared to other light sources.

The oxygen measurement is carried out optionally by a paramagnetic oxygen sensor or an electrochemical cell.

A small PC with 7" colour display and an app-based menu allow an intuitive operation on site as well as remotely.

LOWEST MEASURING RANGES	
Component	Measuring range
NO:	050 mg/m³
NO ₂ :	0100 mg/m ³
SO ₂ :	050 mg/m³
0 ₂ :	025 vol. %
Other components (e.g. CH_2O , H_2S , CI_2) and measuring ranges on request.	

YOUR BENEFITS AT A GLANCE

- mobile cold-dry gas analyser in compact design
- · easy placement directly at the measuring point
- · long-term stable signal
- · user-friendly touch display
- extension of measuring components without additional hardware possible
- remote access

PRECONDITIONS ON SITE

- installation place indoors and dust-free
- · protection against wetness
- protection against percussions/vibrations
- appropriate gas sampling and conditioning*
- * gas conditioning unit available (option)



SCHEMATIC DESIGN



TECHNICAL DATA

FUNCTION

The function of the UV analyser is based on the measurement of an integrated spectrometer in the spectral range of ultraviolet radiation of 180 to 400 nm. Fundamentally, the device is composed of light source, measuring cell and spectrometer which are interconnected via the optical path. The emitted radiation is absorbed partly by the process gas in the measuring cell and detected by a spectrometer afterwards. By using a chemometric model the gas component as well as the concentration can be determined.

Because of the modular design, there is the possibility for application of different spectrometers for adaptation to variable requirements.

Housing:	robust housing with compact 19" format, IP40; design as portable case; 530 mm x 162 mm x 530 mm (w x h x d), approx. 20 kg
Measuring methods:	 spectrometer 180-400 nm (NO₂, SO₂, NO, CH₂O, H₂S, Cl₂) electrochemical cell (optional for O₂) paramagnetic measuring method (optional for O₂)
Number of meas. components:	up to 12 components (dependent on application) and oxygen
Accuracy of spectrometer components:	< 2% of the respective measuring range
Paramagnetic oxygen sensor:	 warm-up time: < 1 h (at 20 °C ambient temperature) zero point drift: < ± 0.1% O2 / week (possibly higher at first commissioning or after longer storage) temperature influence: at zero point setting: < ± 0.05% O2 / °C at reference point setting: < ± 0.2% of meas. value / °C
Ambient conditions:	540 °C (temperature stability max. 5 K/h); humidity: max. 90% (non-condensing)
Optical bench:	 path length of measuring cell: adjustable, 730 mm particle filter: 2 μm
Zero point setting:	automatically with ambient air
Measuring gas conveyance:	via internal pump: • flow rate: max. 2.6 l/min • pressure: max. 1 bar • vacuum: max. 350 mbar
Display / Operating:	7" touch display, 800 x 480 Pixel, status messages for failure, maintenance and maintenance request; Language selection: German, English, French, Chinese
Data storage:	data logger function
Interfaces:	RS232 (Modbus)
Inputs/outputs:	 8 analogue outputs, 420 mA, potential-free, burden max. 500 Ω 14 digital inputs (optocoupler), max. 30 V 16 digital outputs, potential-free, max. 60 V, 500 mA
Remote control:	VNC, remote control via PC
Power supply:	110-250 V AC / 50-60 Hz, 50 W
Other functions:	integrated flow measurement
Optional:	gas conditioning unitgas sampling equipment
Special models are possible on request.	

Dr. Födisch Umweltmesstechnik AG Zwenkauer Strasse 159 • 04420 Markranstädt • Germany Phone: +49 34205 755-0 • Fax: +49 34205 755-40 E-mail: sales@foedisch.de